



471509



**SCHUKO soc. out. hinged cover, splash-protected flush-mtd IP44, p. white glossy**

### Technical Features

#### Electric current

Rated current	16 A
---------------	------

#### Voltage

Rated voltage	250 V
---------------	-------

Nominal voltage	250 - 250 V
-----------------	-------------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	Polar white
--------	-------------

RAL code	9010
----------	------

Surface finish	Glossy
----------------	--------

Material	Thermoplastic
----------	---------------

Treatment	Untreated
-----------	-----------

#### Dimensions

Height	71 mm
--------	-------

Width	71 mm
-------	-------

Depth	53.50 mm
-------	----------

Built-in depth flush-mounted boxes	31 mm
------------------------------------	-------

Built-in depth	31.20 mm
----------------	----------

#### Connection

Connector/plug type	Plug clamp
---------------------	------------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Mounting type	Screw mounting Claw mounting
---------------	---------------------------------

#### Equipment

Connector/plug type socket outlet	SCHUKO
-----------------------------------	--------

Rotated central insert	No
------------------------	----

With hinged lid	Yes
-----------------	-----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

With lock	No
-----------	----

#### Accessories

Has labelling field	No
---------------------	----

#### Cover, door

Type of lid	Self-closing hinged cover
-------------	---------------------------

#### Capacity

Number of modules	1
-------------------	---

#### Safety

With enhanced contact protection	No
----------------------------------	----

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP44
-------------------------------	------

#### Functions

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

**Texts**

Imprint	Without imprint
Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

**Sustainability**

Halogen free	Yes
RoHS conform	Yes