



3037

**Intermediate switch, light control**

**Technical Features**

**Electric current**

Switching current 10 AX (100W LED (SBL))

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Surface finish Matt

Material Metal  
Plastic

**Identification**

Assembly arrangement Basic element

**Connectivity**

Mounting type Claw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 71 x 71 mm

Built-in depth 32 mm

Built-in depth flush-mounted boxes 35 mm

**Safety**

Impact resistance IK IK07

**Electric current**

Rated current 10 A

**Texts**

Installation mode With spreader claws

Type of connection With plug-in terminals

Lighting For lighting and monitoring circuit

Push button No

**Sustainability**

Halogen free Yes

RoHS conform Yes