



3037

Intermediate switch, light control

Technical Features

Electric current	
Switching current	10 AX (100W LED (SBL))
Installation, mounting	
Mounting on	Flush mounting
Voltage	
Rated voltage	250 V
Frequency	
Frequency	50 - 60 Hz
Materials	
Surface finish	Matt
Material	Metal Plastic
Identification	
Assembly arrangement	Basic element
Connectivity	
Mounting type	Claw mounting
Controls and indicators	
Number of buttons	1
Dimensions	
Dimensions	71 x 71 mm
Built-in depth	32 mm
Built-in depth flush-mounted boxes	35 mm
Safety	
Ingress Protection (IP) class	IP20
Impact resistance IK	IK07
Architecture	
Control/operation element	Single rocker
Electric current	
Rated current	10 A
Texts	
Installation mode	With spreader claws
Type of connection	With plug-in terminals
Lighting	For lighting and monitoring circuit
Switch mode	Intermediate
Sustainability	
RoHS conform	Yes