



5036



### Push-button change-over contact illuminated

#### Technical Features

##### Electric current

Switching current	10 A
Momentary contact current	10 A

##### Voltage

Rated voltage	250 V
---------------	-------

##### Architecture

Number of poles	1
-----------------	---

##### Materials

Material	Metal Plastic
Transparent	No

##### Dimensions

Height	71 mm
Width	71 mm
Depth	42 mm
Built-in depth	31 mm
Built-in depth flush-mounted boxes	34 mm

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

##### Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

##### Accessories

Has labelling field	No
---------------------	----

##### Texts

Imprint	Without imprint
Installation mode	With spreader claws
Lighting	For lighting and monitoring circuit
Switch mode	Change-over contact, usable as NC or NO
Type of connection	With plug-in terminals

##### Suitable for

K.x / Q.x / R.x / S.x/B.x

##### Sustainability

Halogen free	Yes
RoHS conform	Yes