



474520

SCHUKO soc. out., mounting orient. var. in 45° steps, 1930/glass, p.white glossy

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Voltage

| | |
|-----------------|-------------|
| Rated voltage | 250 V |
| Nominal voltage | 250 - 250 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Materials

| | |
|----------------|-------------|
| Colour | Polar white |
| RAL code | 9010 |
| Surface finish | Glossy |
| Material | Duroplastic |
| Treatment | Untreated |

Dimensions

| | |
|------------------------------------|-------|
| Height | 71 mm |
| Width | 71 mm |
| Depth | 42 mm |
| Number of units | 1 |
| Built-in depth flush-mounted boxes | 31 mm |
| Built-in depth | 32 mm |

Connection

| | |
|---------------------|------------|
| Connector/plug type | Plug clamp |
|---------------------|------------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Connectivity

| | |
|--------------------|---------------------------------|
| Type of connection | Plug-in connection |
| Mounting type | Screw mounting Claw mounting |

Equipment

| | |
|-----------------------------------|--------|
| Connector/plug type socket outlet | SCHUKO |
| Rotated central insert | Yes |
| With hinged lid | No |
| With round protective earth pin | No |
| With signal lamp | No |
| With lock | No |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Safety

| | |
|----------------------------------|------|
| With enhanced contact protection | No |
| Impact resistance IK | IK02 |
| Ingress Protection (IP) class | IP20 |

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting | No |

Texts

| | |
|--------------------|-------------------------------------|
| Imprint | Without imprint |
| Cover | Central cover plate |
| Protection | Without enhanced contact protection |
| Type of connection | With plug-in terminals |

Suitable for

Serie 1930 / Serie Glas

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |