



47231606

## SCHUKO soc. out., enhncd contact prot., B.3/B.7, ant., matt

### Technical Features

#### Electric current

Rated current	16 A
---------------	------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	Anthracite
RAL code	7021
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

#### Dimensions

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

#### Connection

Connector/plug type	Plug-in terminal
---------------------	------------------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

#### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

#### Accessories

Has labelling field	No
---------------------	----

#### Safety

With enhanced contact protection	Yes
Ingress Protection (IP) class	IP20

#### Texts

Imprint	Without imprint
Protection	Enhanced contact protection
Type of connection	With plug-in terminals

#### Suitable for

S.x/B.x	
---------	--

#### Sustainability

Halogen free	Yes
RoHS conform	Yes