



47231909

SCHUKO soc. out., enhncd contact prot., S.1/B.3/B.7, p. white, matt, plastic

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Materials

Colour Polar white
RAL code 9010
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Dimensions

Width 71 mm
Number of units 1
Built-in depth flush-mounted boxes 31 mm
Built-in depth 32 mm

Connection

Connector/plug type Plug-in terminal

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection
Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO
Rotated central insert No
With hinged lid No
With round protective earth pin No
With signal lamp No
With lock No

Accessories

Has labelling field No

Safety

With enhanced contact protection Yes
Ingress Protection (IP) class IP20

Identification

With imprint No

Texts

Protection Enhanced contact protection
Type of connection With plug-in terminals

Suitable for

S.x/B.x

Sustainability

Halogen free Yes
RoHS conform Yes