



47157006

Schuko socket outlet K.1 anthracite matt lacquered

Technical Features

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Materials

| | |
|----------------|---------------|
| Colour | Anthracite |
| RAL code | 7021 |
| Surface finish | Matt |
| Material | Thermoplastic |
| Treatment | Varnished |

Dimensions

| | |
|-----------------|-------|
| Height | 71 mm |
| Width | 71 mm |
| Number of units | 1 |
| Built-in depth | 32 mm |

Connection

| | |
|---------------------|------------------|
| Connector/plug type | Plug-in terminal |
|---------------------|------------------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Connectivity

| | |
|--------------------|---------------------------------|
| Type of connection | Plug-in connection |
| Mounting type | Screw mounting Claw mounting |

Equipment

| | |
|-----------------------------------|--------|
| Connector/plug type socket outlet | SCHUKO |
| Rotated central insert | No |
| With hinged lid | No |
| With round protective earth pin | No |
| With signal lamp | No |
| With lock | No |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Safety

| | |
|----------------------------------|------|
| With enhanced contact protection | No |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP20 |

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting | No |

Identification

| | |
|--------------|----|
| With imprint | No |
|--------------|----|

Texts

| | |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

Texts

Type of connection

With plug-in terminals

Suitable for

K.x