



47431909

SCHUKO soc. out., S.1/B.3/B.7, p. white, matt, plastic

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Materials

Colour Polar white

RAL code 9010

Surface finish Matt

Dimensions

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth 32 mm

Connection

Connector/plug type Plug-in terminal

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field No

Safety

With enhanced contact protection No

Ingress Protection (IP) class IP20

Identification

With imprint No

Texts

Protection Without enhanced contact protection

Type of connection With plug-in terminals

Suitable for

S.x/B.x

Sustainability

Halogen free Yes

RoHS conform Yes