



47431909

SCHUKO soc. out., S.1/B.3/B.7, p. white, matt, plastic

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt

Dimensions

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth	32 mm

Connection

Connector/plug type	Plug clamp
---------------------	------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Safety

With enhanced contact protection	No
Ingress Protection (IP) class	IP20

Texts

Imprint	Without imprint
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

Suitable for

S.x/B.x	
---------	--

Sustainability

Halogen free	Yes
RoHS conform	Yes