



47436086

**SCHUKO soc. out., Q.x, ant. velvety, lacq.**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Materials**

Colour	Anthracite
RAL code	7021
Surface finish	Velvety

**Dimensions**

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth	32 mm

**Connection**

Connector/plug type	Plug-in terminal
---------------------	------------------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
---------------------	----

**Safety**

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

**Identification**

With imprint	No
--------------	----

**Texts**

Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

**Suitable for**

Q.x	
-----	--