



47518989

SCHUKO soc. out. hinged cover, S.1/B.3/B.7, p. white glossy

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Materials

Colour Polar white

RAL code 9010

Surface finish Glossy

Dimensions

Height 71 mm

Width 71 mm

Number of units 1

Connection

Connector/plug type Plug-in terminal

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

With hinged lid Yes

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field No

Cover, door

Type of lid Self-closing hinged cover

Safety

With enhanced contact protection No

Ingress Protection (IP) class IP20

Texts

Imprint With imprint

Protection Without enhanced contact protection

Type of connection With plug-in terminals

Sustainability

Halogen free Yes

RoHS conform Yes