



47238989

**SCHUKO soc. out., enhncd contact prot., S.1/B.3/B.7, p. white glossy**

**Technical Features**

**Electric current**

Rated current	16 A
---------------	------

**Voltage**

Rated voltage	250 V
---------------	-------

**Materials**

Colour	Polar white
RAL code	9010
Material	Duroplastic
Treatment	Untreated

**Dimensions**

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

**Connection**

Connector/plug type	Plug-in terminal
---------------------	------------------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
---------------------	----

**Safety**

With enhanced contact protection	Yes
Ingress Protection (IP) class	IP20

**Texts**

Imprint	Without imprint
Protection	Enhanced contact protection
Type of connection	With plug-in terminals

**Suitable for**

S.x/B.x	
---------	--

**Sustainability**

Halogen free	Yes
RoHS conform	Yes