



47733515



SCHUKO soc.out. 3gang hor. hinged cover surface-mtd, W.1, grey/light grey matt

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Grey
RAL code 7011
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Dimensions

Height 76 mm
Width 218 mm
Built-in depth flush-mounted boxes 0 mm

Installation, mounting

Mounting on Surface mounting

Connectivity

Type of connection Plug-in connection
Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO
Rotated central insert No
With hinged lid Yes
With round protective earth pin No
With signal lamp No
With lock No

Accessories

Has labelling field No

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules 3

Safety

With enhanced contact protection No
Impact resistance IK IK05
Ingress Protection (IP) class IP55

Functions

With orientation lighting No
With function lighting No

Identification

With imprint No

Texts

Cover	Complete housing
Wiring	Inserts wired-through
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals
Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor

Sustainability

Halogen free	Yes
RoHS conform	Yes