



EGN400AU



**Multi-function time switch 4 channels bluetooth**

**Technical Features**

**Voltage**

Nominal voltage	230 - 230 V
Rated operational voltage Ue	230 - 230 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power**

230 V incandescent and halogen lamp	2300 W
-------------------------------------	--------

**Lighting**

Max. load fluorescent lamp in series	1000 W
Max. load fluorescent lamp parallel compensated	400 VA

**Functions**

Power reserve in years	10 y
With network synchronisation	Yes
With quartz synchronisation	Yes
Number of function channels	4

**Equipment**

Accuracy per day	0.25 s
With impulse programme	Yes
Number of channels	4

**Connection**

Type of contacts	1x changeover
------------------	---------------

**Settings**

Daily programme	Yes
Weekly programme	Yes
Annual programme	Yes

**Use conditions**

Operating temperature	-5 - +45 °C
-----------------------	-------------

**Connection**

Cross-section flexible conductor	0.2 - 2.5 mm <sup>2</sup>
Cross-section rigid conductor	0.2 - 4 mm <sup>2</sup>

**Texts**

Type of connection	With screw terminal
--------------------	---------------------

**Dimensions**

Height	90 mm
Width	72 mm
Depth	61.60 mm

**Main electrical attributes**

Minimum interval between 2 switching times	1 min
--	-------

**Capacity**

Number of modules	4
-------------------	---

**Sustainability**

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

