



TYAS624D

Output device for 4 shutters / blinds 24V DC

Technical Features

Settings

| | |
|------------------------------|-------------|
| Supported configuration mode | ETS easy |
|------------------------------|-------------|

Connectivity

| | |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

Installation, mounting

| | |
|-------------|----------|
| Mounting on | DIN rail |
|-------------|----------|

Materials

| | |
|--------|------------|
| Colour | Light grey |
|--------|------------|

Equipment

| | |
|-------------------------------|-----|
| With switch for manual switch | Yes |
|-------------------------------|-----|

Electric current

| | |
|------------------------|-----|
| Rated current | 6 A |
| Max. switching current | 6 A |

Voltage

| | |
|----------------------------|-----------|
| Operating voltage over bus | 21 - 32 V |
|----------------------------|-----------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Connection

| | |
|----------------------------------|----------------------------|
| Cross-section flexible conductor | 0.75 - 2.5 mm ² |
| Cross-section rigid conductor | 0.75 - 2.5 mm ² |

Capacity

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Power

| | |
|--|-------|
| Rated operational power under 230 V AC AC1 | 144 W |
|--|-------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|