Product Datasheet
TYAS624D



TYAS624D

Output device for 4 shutters / blinds 24V DC

Technical Features

Settings

Supported configuration mode	ETS easy

Connectivity

With bus system KNX radio	No

Installation, mounting

Mounting on	DIN rail

Materials

Colour	Light grey

Equipment

With switch for manual switch	Yes

Electric current

Rated current IN	6 A
Max. switching current	6 A

Voltage

Operating voltage over bus	21 - 32 V
Output voltage	24 - 24 V
Type voltage supply	DC

Use conditions

Operating temperature	-5 - 45 °C

Connection

Cross-section flexible conductor	0.75 - 2.5 mm^2
Cross-section rigid conductor	0.75 - 2.5 mm^2

Capacity

Number of modules	4

Power

Rated operational power under 230 V AC AC1	144 W

Data act compliance

Is generating data	Yes
Data types	Basic information On/Off status Scenes Shade configuration Window covering
Data formats	KNX (TP)
Estimated daily data volume	10 KB - 100 KB
Real time data generation	Yes
Data stored on device	No

Sustainability

RoHS conform	Yes