



TYAS610D

**Output module 10-fold 16a c-load adapted**

**Technical Features**

**Settings**

Supported configuration mode	ETS easy
------------------------------	-------------

**Connectivity**

With bus system KNX	Yes
With bus system KNX radio	No

**Dimensions**

Height	90 mm
Depth	62.5 mm
Number of width units	6

**Electric current**

Rated current	16 A
---------------	------

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Architecture**

Bus system	KNX
------------	-----

**Materials**

Colour	Light grey
--------	------------

**Equipment**

Radio frequency bidirectional	No
With switch for manual switch	Yes

**Electric current**

Bus current consumption while idle	8 mA
------------------------------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power**

Power incandescent lamp 230 V	2300 - 2300 W
Output power	2300 W
230 V incandescent and halogen lamp	2300 W
Power incandescent lamp	2300 - 2300 W

**Voltage**

Rated operational voltage Ue	230 - 230 V
System supply voltage	30 V DC Via bus
Operating voltage over bus	21 - 32 V

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Connection**

Cross-section rigid conductor	0.75 - 2.5 mm <sup>2</sup>
Cross-section flexible conductor	0.75 - 2.5 mm <sup>2</sup>

**Sustainability**

RoHS conform	Yes
--------------	-----