



WGDS113S1USBAC

13A SINGLE SWITCHED SOCKET WITH 2 PORT TYPE A + C

Technical Features

Voltage

Rated voltage 230 V

Electric current

Rated current 13 A

Use conditions

Operating temperature -20 - 35 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

Dimensions

Height 86 mm

Width 86 mm

Depth 30 mm

Built-in depth flush-mounted boxes 30 mm

Built-in depth 30 mm

Connection

Connector/plug type Screw terminal

Installation, mounting

Connection on Busbar

Mounting on Flush mounting

Mounting-/Connection Position In housing

Connectivity

Type of connection Screw connection

With claw mounting No

Mounting type Screw mounting

Equipment

With signal lamp No

Accessories

Has labelling field No

Capacity

Number of modules 0

Controls and indicators

Type of lighting for the installation devices Integrated operating control light

Safety

Impact resistance IK IK02

Ingress Protection (IP) class IP3X

Suitable for

shark

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes