



JKD1148TM

**125A Power & Lighting Board 14/8 Pan Assemblies MID**

**Technical Features**

**Architecture**

Number of poles 3

**Functions**

Has protection main switch Yes

**Installation, mounting**

Suitable for outdoor usage No

**Capacity**

Number of modules 66

**Voltage**

Nominal voltage 415 - 415 V

**Electric current**

Rated current 125 A

**Dimensions**

Depth 165.5 mm

Height 1400 mm

Width 465 mm

**Cover, door**

Door/cover is transparent Yes

**Materials**

Colour Light grey

Material Steel

**Equipment**

With energy meter Yes

**Safety**

Impact resistance IK IK05

Ingress Protection (IP) class IP30

Protection class Isolation class III