



JKD1814TM

125A Power & Lighting Board 8/14 Pan Assemblies MID

Technical Features

Architecture

Number of poles 3

Functions

Has protection main switch Yes

Installation, mounting

Suitable for outdoor usage No

Capacity

Number of modules 66

Voltage

Nominal voltage 415 - 415 V

Electric current

Rated current 125 A

Dimensions

Depth 165.5 mm

Height 1400 mm

Width 465 mm

Cover, door

Door/cover is transparent Yes

Materials

Colour Light grey

Material Steel

Equipment

With energy meter Yes

Safety

Impact resistance IK IK05

Ingress Protection (IP) class IP30

Protection class Isolation class III