



WBHP2VS

**Allure 10A Vertical Double Socket Gloss White**

**Technical Features**

**Voltage**

Rated voltage	240 V
---------------	-------

**Electric current**

Rated current	10 A
---------------	------

**Voltage**

Output voltage	230 - 250 V
----------------	-------------

**Power**

Power consumption standby	0 W
---------------------------	-----

**Materials**

Colour	White
RAL code	9010
Surface finish	Glossy
Material	Polycarbonate (PC)
Contains recycled material (% of total plastic weight)	0 %

**Dimensions**

Height	120 mm
Width	82 mm
Depth	9.5 mm
Built-in depth	20 mm

**Connection**

Connector/plug type	Australian standard AS/NZS 3112
Number of conduit inlets	0

**Installation, mounting**

Mounting on	Surface mounting
Mounting-/Connection Position	Back

**Connectivity**

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
Pre-equipped with	None

**Cover, door**

Type of lid	Without lid
-------------	-------------

**Capacity**

Number of modules	0
-------------------	---

**Safety**

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP2X

---

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

**Texts**

Cover	Full cover plate
Lighting	Without neon lamp
Wiring	With earth connection
Protection	No
Labelling	Without labelling
Terminal	With mains connection terminals

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes