



WBHP2VS

Allure 10A Vertical Double Socket Gloss White

Technical Features

Voltage

Rated voltage	240 V
---------------	-------

Electric current

Rated current	10 A
---------------	------

Voltage

Output voltage	230 - 250 V
----------------	-------------

Power

Power consumption standby	0 W
---------------------------	-----

Materials

Colour	White
RAL code	9010
Surface finish	Glossy
Material	Polycarbonate (PC)
Contains recycled material (% of total plastic weight)	0 %

Dimensions

Height	120 mm
Width	82 mm
Depth	9.5 mm
Built-in depth	20 mm

Connection

Connector/plug type	Australian standard AS/NZS 3112
---------------------	---------------------------------

Installation, mounting

Mounting on	Surface mounting
Mounting-/Connection Position	Back

Connectivity

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
Pre-equipped with	None

Cover, door

Type of lid	Without lid
-------------	-------------

Capacity

Number of modules	0
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP2X

Product Datasheet

WBHP2VS

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Imprint	Without imprint
Cover	Full cover plate
Lighting	Without neon lamp
Wiring	With earth connection
Protection	No
Labelling	Without labelling
Terminal	With mains connection terminals

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes