



WBHP2VS

Allure 10A Vertical Double Socket Gloss White

Technical Features

Voltage

Rated voltage	240 V
---------------	-------

Electric current

Rated current	10 A
---------------	------

Voltage

Output voltage	230 - 250 V
----------------	-------------

Power

Power consumption standby	0 W
---------------------------	-----

Materials

Colour	White
RAL code	9010
Surface finish	Glossy
Material	Polycarbonate (PC)
Contains recycled material (% of total plastic weight)	0 %

Dimensions

Height	120 mm
Width	82 mm
Depth	9.5 mm
Built-in depth	20 mm

Connection

Connector/plug type	Australian standard AS/NZS 3112
Number of conduit inlets	0

Installation, mounting

Mounting on	Surface mounting
Mounting-/Connection Position	Back

Connectivity

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
Pre-equipped with	None

Cover, door

Type of lid	Without lid
-------------	-------------

Capacity

Number of modules	0
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP2X

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	Full cover plate
Lighting	Without neon lamp
Wiring	With earth connection
Protection	No
Labelling	Without labelling
Terminal	With mains connection terminals

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes