



XVR111C

### Charging Station witty one 1x11kW 3ph+N attached cable T2 6.5m

#### Technical Features

##### Power

Power per charging point	11 kW
Connected load	0.1 - 11 kW

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Power supply

Number of phases for power supply	3
-----------------------------------	---

##### Electric current

Rated current	16 A
---------------	------

##### Connectivity

Number of charging points	1
---------------------------	---

##### Functions

With load management	No
----------------------	----

##### Equipment

Number of house sockets	0
With circuit breaker	No
With emergency release at power failure	Yes

##### Connection

Connector/plug type	Type 2
---------------------	--------

##### Dimensions

Dimensions	370 x 250 mm
Height	370 mm
Width	250 mm
Depth	150 mm

##### Installation, mounting

Mounting on	Wall mounting
-------------	---------------

##### Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK10

##### Use conditions

Operating temperature	-25 - 50 °C
-----------------------	-------------

##### Voltage

Nominal voltage	230 - 400 V
-----------------	-------------

##### Materials

Material	Plastic
----------	---------

**Illustrations | Drawings**

