




WGDT2RJ6EG

RJ45 outlet cat6 (2mod);eg

Technical Features

Frequency

Transmission bandwidth	0-250 MHz
------------------------	-----------

Equipment

With transparent label holder	No
Number of outputs	2

Use conditions

Operating temperature	-20-45 °C
-----------------------	-----------

Equipment

With hinged lid	No
-----------------	----

Materials

Colour	Gold
--------	------

Connection

Connector/plug type	RJ45
---------------------	------

Materials

Material	Polycarbonate (PC)
----------	--------------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Voltage

Rated voltage	0 V
---------------	-----

Electric current

Rated current	0 A
---------------	-----

Dimensions

Built-in depth	27 mm
----------------	-------

Texts

Outlet	With straight outlet
Protection	With dust protection sliders
Supporting plate/supporting ring	With supporting plate