



WGDT1RJ

### RJ11 outlet (1mod)

#### Technical Features

##### Frequency

|                        |           |
|------------------------|-----------|
| Transmission bandwidth | 0-100 MHz |
|------------------------|-----------|

##### Equipment

|                               |    |
|-------------------------------|----|
| With transparent label holder | No |
| Number of outputs             | 1  |

##### Use conditions

|                       |           |
|-----------------------|-----------|
| Operating temperature | -20-45 °C |
|-----------------------|-----------|

##### Equipment

|                 |    |
|-----------------|----|
| With hinged lid | No |
|-----------------|----|

##### Materials

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

##### Connection

|                     |      |
|---------------------|------|
| Connector/plug type | RJ45 |
|---------------------|------|

##### Materials

|          |                    |
|----------|--------------------|
| Material | Polycarbonate (PC) |
|----------|--------------------|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Voltage

|               |     |
|---------------|-----|
| Rated voltage | 0 V |
|---------------|-----|

##### Electric current

|               |     |
|---------------|-----|
| Rated current | 0 A |
|---------------|-----|

##### Dimensions

|                |       |
|----------------|-------|
| Built-in depth | 27 mm |
|----------------|-------|

##### Texts

|                                  |                       |
|----------------------------------|-----------------------|
| Supporting plate/supporting ring | With supporting plate |
|----------------------------------|-----------------------|