



WGDT1RJ5IG

RJ45 outlet cat5e (1mod);ig

Technical Features

Frequency

| | |
|------------------------|-----------|
| Transmission bandwidth | 0-100 MHz |
|------------------------|-----------|

Equipment

| | |
|-------------------------------|----|
| With transparent label holder | No |
| Number of outputs | 1 |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -20 - 45 °C |
|-----------------------|-------------|

Equipment

| | |
|-----------------|----|
| With hinged lid | No |
|-----------------|----|

Materials

| | |
|--------|-------------------|
| Colour | Interstellar grey |
|--------|-------------------|

Connection

| | |
|---------------------|------|
| Connector/plug type | RJ45 |
|---------------------|------|

Materials

| | |
|----------|--------------------|
| Material | Polycarbonate (PC) |
|----------|--------------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Voltage

| | |
|---------------|-----|
| Rated voltage | 0 V |
|---------------|-----|

Electric current

| | |
|---------------|-----|
| Rated current | 0 A |
|---------------|-----|

Dimensions

| | |
|----------------|-------|
| Built-in depth | 27 mm |
|----------------|-------|

Texts

| | |
|----------------------------------|-----------------------------|
| Outlet | With straight outlet |
| Protection | With dust protection slider |
| Supporting plate/supporting ring | With supporting plate |