



WGCXT1RJ6NMKB

RJ45 outlet cat6 (1mod) wo/symbol;kb

Technical Features

Frequency

Transmission bandwidth 0-250 MHz

Equipment

With transparent label holder No

Number of outputs 1

Use conditions

Operating temperature -20 - 45 °C

Equipment

With hinged lid No

Materials

Colour Knight black

Connection

Connector/plug type RJ45

Materials

Material Polycarbonate (PC)

Safety

Ingress Protection (IP) class IP20

Voltage

Rated voltage 0 V

Electric current

Rated current 0 A

Dimensions

Built-in depth 27 mm