



HSX028H

**Closing Coil 415V AC HWS (CC)**

**Technical Features**

**Power**

Inrush power absorbed	200 VA
Operating consumption	5 VA

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Voltage**

Command voltage AC	380 - 480 V
Rated insulation voltage $U_i$	480 V
Rated impulse withstand voltage $U_{imp}$	6000 V
Overvoltage category according to IEC 60947-1	2

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes