



HSX033H

**Undervoltage trip 240V AC HWS (UV)**

**Technical Features**

**Power**

Inrush power absorbed	200 VA
Operating consumption	5 VA
Total power loss under IN	5 W

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Voltage**

Command voltage AC	200 - 250 V
Command voltage DC	200 - 250 V
Rated insulation voltage $U_i$	480 V
Rated impulse withstand voltage $U_{imp}$	6000 V

**Functions**

Delayed	No
---------	----

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes