



HSX042H

Auxilliary Switch 4NO+4NC HWS (AX)

Technical Features

Electric current

Rated current 230 V AC15 2 A

Connectivity

Mounting type Click mounting

Frequency

Frequency 50 - 60 Hz

Use conditions

Storage/transport temperature -40 - 70 °C

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes