



HMQ990AR

Load Break Switch Disconnecter h3+ PW1600 3P 1600A FTC

Technical Features

Electric current

Rated current	1600 A
Rated short-time withstand current Icw IEC 60947	19.2 kA
Rated current 10°C according to IEC 60947	1600 A
Rated current 15°C according to IEC 60947	1600 A
Rated current 20°C according to IEC 60947	1600 A
Rated current 25°C according to IEC 60947	1600 A
Rated current 30°C according to IEC 60947	1600 A
Rated current at 35°C according to IEC 60947	1600 A
Rated current at 40°C according to IEC 60947	1600 A
Rated current 45°C according to IEC 60947	1600 A
Rated current 50°C according to IEC 60947	1590 A
Rated current 55°C according to IEC 60947	1540 A
Rated current at 60°C according to IEC 60947	1490 A
Rated current 65°C according to IEC 60947	1430 A
Rated current 70°C according to IEC 60947	1430 A

Architecture

Number of poles	3
Control/operation element	Toggle

Voltage

Rated insulation voltage Ui	1000 V
Rated impulse withstand voltage Uimp	8 kV

Frequency

Frequency	50 - 60 Hz
-----------	------------

Functions

Trip unit	Switch
-----------	--------

Sustainability

RoHS conform	Yes
--------------	-----