



HW4E325DB

**ACB HW4 66kA 2500A 3P Drawout TU sentinel LSI, VCVC**

**Technical Features**

**Electric current**

Rated current	2500 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	66 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	66 kA
Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2	66 kA

**Endurance**

Number of mechanical operations	20000
---------------------------------	-------

**Voltage**

Rated insulation voltage U <sub>i</sub>	1000 V
Rated impulse withstand voltage U <sub>imp</sub>	12000 V
Type voltage supply	AC

**Resistance**

Internal resistance	13 μΩ
---------------------	-------

**Architecture**

Number of poles	3
Number of protected poles	3
Device construction type	Drawout
Type of pole	3P3D

**Power**

Total power loss under I <sub>N</sub>	226.40 W
---------------------------------------	----------

**Sustainability**

RoHS conform	Yes
--------------	-----