



HW2E316FE

ACB HW2 66kA 1600A 3P Fixed TU sentinel Energy LSI, VCVC

Technical Features

Electric current

Rated current	1600 A
Rated ultimate short-circuit breaking capacity I_{cu} under 400 V AC IEC 60947-2	66 kA
Rated service breaking capacity I_{cs} under 230 V AC according to IEC 60947-2	66 kA
Rated service breaking capacity I_{cs} under 400 V AC according to IEC 60947-2	66 kA

Voltage

Rated insulation voltage U_i	1000 V
Rated impulse withstand voltage U_{imp}	12000 V
Type voltage supply	AC

Architecture

Number of poles	3
Type of pole	3P3D

Tripping

Time of response when closing	50 ms
-------------------------------	-------

Architecture

Device construction type	Fixed built-in
--------------------------	----------------

Sustainability

RoHS conform	Yes
--------------	-----