



HE2W320DSAVAAAAAA

Switch HW2 2000A 3P Drawout, VCVC

Technical Features

Electric current

Rated current	2000 A
Rated short-time withstand current I _{cw} t=1 s 220 - 240 V AC according to IEC 60947 - 3	66 kA
Rated short-time withstand current I _{cw} t=1 s 380 - 415 V AC according to IEC 60947 - 3	66 kA

Architecture

Number of poles	3
Device construction type	Drawout

Voltage

Rated insulation voltage U _i	1000 V
Rated impulse withstand voltage U _{imp}	12000 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes