



HW4E332DB

ACB HW4 66kA 3200A 3P Drawout TU sentinel LSI, VCVC

Technical Features

Electric current

Rated current	3200 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	66 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	66 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	66 kA

Endurance

Number of mechanical operations	20000
---------------------------------	-------

Voltage

Rated insulation voltage Ui	1000 V
Rated impulse withstand voltage Uimp	12000 V
Type voltage supply	AC

Resistance

Internal resistance	13 $\mu\Omega$
---------------------	----------------

Architecture

Number of poles	3
Number of protected poles	3
Device construction type	Drawout
Type of pole	3P3D

Power

Total power loss under IN	496.80 W
---------------------------	----------

Sustainability

RoHS conform	Yes
--------------	-----