



HWIN308FB

ACB HW1 42kA 800A 3P Fixed TU sentinel LSI, VCVC

Technical Features

Electric current

Rated current	800 A
Rated ultimate short-circuit breaking capacity I_{cu} under 400 V AC IEC 60947-2	42 kA
Rated service breaking capacity I_{cs} under 230 V AC according to IEC 60947-2	42 kA
Rated service breaking capacity I_{cs} under 400 V AC according to IEC 60947-2	42 kA

Endurance

Electric endurance in number of cycles	8000
Number of mechanical operations	30000

Voltage

Rated insulation voltage U_i	1000 V
Rated impulse withstand voltage U_{imp}	12000 V
Type voltage supply	AC

Resistance

Internal resistance	25 $\mu\Omega$
---------------------	----------------

Architecture

Number of poles	3
Device construction type	Fixed built-in

Tripping

Time of response when closing	45 ms
-------------------------------	-------