



HW2W320FS

Switch HW2 2000A 3P Fixed, VCVV

Technical Features

Electric current

| | |
|---------------|--------|
| Rated current | 2000 A |
|---------------|--------|

Architecture

| | |
|--------------------------|----------------|
| Number of poles | 3 |
| Device construction type | Fixed built-in |

Voltage

| | |
|---|---------|
| Rated insulation voltage U_i | 1000 V |
| Rated impulse withstand voltage U_{imp} | 12000 V |

Electric current

| | |
|--|-------|
| Rated short-time withstand current I_{cw} $t=1s$ 220 - 240 V AC according to IEC 60947 - 3 | 66 kA |
| Rated short-time withstand current I_{cw} $t=1s$ 380 - 415 V AC according to IEC 60947 - 3 | 66 kA |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -25 - 70 °C |
|-----------------------|-------------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |