



HW2W320FS

Switch HW2 2000A 3P Fixed, VCV

Technical Features

Electric current

Rated current	2000 A
---------------	--------

Architecture

Number of poles	3
Device construction type	Fixed built-in

Voltage

Rated insulation voltage Ui	1000 V
Rated impulse withstand voltage Uimp	12000 V

Electric current

Rated short-time withstand current Icw t=1 S 220 - 240 V AC according to IEC 60947 - 3	66 kA
Rated short-time withstand current Icw t=1 S 380 - 415 V AC according to IEC 60947 - 3	66 kA

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes