



HW2W410FS

Switch HW2 1000A 4P Fixed, VCVC

Technical Features

Electric current

Rated current	1000 A
---------------	--------

Architecture

Number of poles	4
Device construction type	Fixed built-in

Voltage

Rated insulation voltage U_i	1000 V
Rated impulse withstand voltage U_{imp}	12000 V

Electric current

Rated short-time withstand current I_{cw} $t=1s$ 220 - 240 V AC according to IEC 60947 - 3	66 kA
Rated short-time withstand current I_{cw} $t=1s$ 380 - 415 V AC according to IEC 60947 - 3	66 kA

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes