



WBMHDMIL - HDMI rotoloc flex mech

HDMI rotoloc F/F with flexible lead

Technical Features

Connection

Connector/plug type	HDMI
Number of connections	1

Dimensions

Built-in depth flush-mounted boxes	150 mm
Depth	150 mm
Height	23 mm
Width	23 mm

Equipment

With dust cover	No
With hinged lid	No

Materials

Material	Plastic
Colour	White
Surface finish	Matt

Frequency

Frequency video	144 MHz
-----------------	---------

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP00

Dimensions

Built-in depth	150 mm
----------------	--------

Use conditions

Operating temperature	0 - 40 °C
-----------------------	-----------

Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Texts

Installation mode	For surface mounting with mounting plate
-------------------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes