



XVR111C

Charging station witty plus 1x22kW 1/3ph+N att. cable

Technical Features

Power

Power per charging point	22 kW
Connected load	0.1 - 22 kW

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power supply

Number of phases for power supply	1
	3

Electric current

Rated current	32 A
---------------	------

Connectivity

Number of charging points	1
---------------------------	---

Functions

With load management	Yes
----------------------	-----

Equipment

Number of house sockets	0
With circuit breaker	No
With emergency release at power failure	Yes

Connection

Connector/plug type	Type 2
---------------------	--------

Dimensions

Dimensions	370 x 250 mm
Height	370 mm
Width	250 mm
Depth	150 mm

Installation, mounting

Mounting on	Wall mounting
-------------	---------------

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK10

Use conditions

Operating temperature	-25 - 50 °C
-----------------------	-------------

Voltage

Nominal voltage	230-240 V
-----------------	-----------

Materials

Material	Plastic
----------	---------

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

