



HSY034H

Undervoltage Time Delay Controller 415V AC

Technical Features

Connection

Cross-section of input and output with screws, for massive conductors	0.6 - 2.5 mm ²
Cross-section of input and output with screws, for flexible conductors	0.6 - 2.5 mm ²

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Voltage

Command voltage AC	380 - 480 V
--------------------	-------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes