



TYAS664D

KNX-DALI 2 actuator, 4 channels, broadcast, KNX Secure, easy, RGB(T)W

Technical Features

Equipment

Web server	No
------------	----

Voltage

Operating voltage	230 - 240 V
Operating voltage over bus	21 - 32 V
Type voltage supply	AC

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Equipment

Number of channels	4
--------------------	---

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Equipment

Max. number of devices per channel	24
------------------------------------	----

Controls and indicators

With LED indication	Yes
---------------------	-----

Dimensions

Width	44 mm
Dimensions	22.5 x 44 mm
Depth	43 mm
Number of width units	6

Connection

Connector/plug type	DRA (DIN-rail Adapter)
---------------------	------------------------

Sustainability

RoHS conform	Yes
--------------	-----