



WNA001B

IP55

**Change-over switch insert rocker surf.-mtd/flush-mtd, W.1, p.white matt plast LT**

**Technical Features**

**Electric current**

Switching current 10 A

**Installation, mounting**

Mounting on Flush mounting  
Surface mounting

**Voltage**

Rated voltage 250 V

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Polar white  
RAL code 9010  
Surface finish Matt  
Material Thermoplastic  
Treatment Untreated  
Contains recycled material (% of total plastic weight) 0 %

**Identification**

Assembly arrangement Control element

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 70 x 70 mm  
Built-in depth 12 mm  
Built-in depth flush-mounted boxes 0 mm  
Height of P-touch band for labelling field 0 mm

**Safety**

Impact resistance IK IK08  
Usable in higher IP class IP55 with closed cover

**Electric current**

Rated current 10 A

**Connection**

Type of contacts 2-way  
Connector/plug type Turn screw lock

**Texts**

Installation mode For screw fastening  
Type of connection With plug-in terminals  
Push button No  
Imprint Without imprint

**Sustainability**

Halogen free Yes  
REACH-SVHC free Yes  
RoHS conform Yes