



WNA003

IP55

Control change-over switch insert, rocker surf./flush-mtd lens W.1 grey matt LT

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Flush mounting
Surface mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Grey
RAL code 7011
Surface finish Matt
Material Thermoplastic
Treatment Untreated
Contains recycled material (% of total plastic weight) 0 %

Identification

Assembly arrangement Control element

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 70 x 70 mm
Built-in depth 12 mm
Built-in depth flush-mounted boxes 0 mm
Height of P-touch band for labelling field 0 mm

Safety

Impact resistance IK IK08
Usable in higher IP class IP55 with closed cover

Electric current

Rated current 10 A

Connection

Type of contacts 2-way
Connector/plug type Turn screw lock

Texts

Installation mode For screw fastening
Type of connection With N-terminal
With plug-in terminals
Lighting With red 230 V LED unit
For monitoring circuit
Push button No
Imprint Without imprint

Sustainability

REACH-SVHC free Yes
RoHS conform Yes