



WNE008B



**On/off switch insert 2p rocker+impr. 0 + 1 surf.-/flush-mtd,W.1,p.wh.m.plas. LT**

**Technical Features**

**Electric current**

Switching current 10 A

**Installation, mounting**

Mounting on Flush mounting  
Surface mounting

**Voltage**

Rated voltage 250 V

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Polar white  
RAL code 9010  
Surface finish Matt  
Material Thermoplastic  
Treatment Untreated

**Identification**

Assembly arrangement Control element

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 76 x 76 mm  
Built-in depth 12 mm  
Built-in depth flush-mounted boxes 0 mm

**Safety**

Ingress Protection (IP) class IP55  
Impact resistance IK IK08

**Architecture**

Control/operation element Single rocker

**Electric current**

Rated current 10 A

**Connection**

Type of contacts 2-way  
Connector/plug type Turn screw lock

**Texts**

Installation mode For screw fastening  
Type of connection With N-terminal  
With plug-in terminals  
Switch mode 2x 1- -pole off

**Sustainability**

Halogen free Yes  
REACH-SVHC free Yes  
RoHS conform Yes