



WNA010

IP55

Intermediate switch insert rocker surface-mtd/flush-mtd, W.1, grey matt LT

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Materials

Colour	Grey
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No
Contains recycled material (% of total plastic weight)	0 %
Backside internal	Matt

Dimensions

Height	70 mm
Width	70 mm
Depth	42 mm
Built-in depth	12 mm
Built-in depth flush-mounted boxes	40 mm
Height of P-touch band for labelling field	0 mm

Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

Controls and indicators

Indicator lamp	Without
Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Connectivity

Type of connection	quickconnect
With claw mounting	No

Connection

Connector/plug type	Turn screw lock
---------------------	-----------------

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK08

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

Texts

Installation mode	For screw fastening
Switch mode	Intermediate

Texts

Type of connection	With plug-in terminals
--------------------	------------------------

Suitable for

cubyko

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes
