



WNA105



sock.outl. insert w. earth.pin a. hing. cov. SM/flush-mounted, cont.prot., W.1

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Polycarbonate (PC) Polypropylene (PP)
Treatment	Untreated

Dimensions

Height	75 mm
Width	75 mm
Depth	22.80 mm
Number of units	1
Built-in depth flush-mounted boxes	35 mm

Connection

Connector/plug type	Turn screw lock
---------------------	-----------------

Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No
With lock	No

Accessories

Has labelling field	Yes
---------------------	-----

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK08
Ingress Protection (IP) class	IP55

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Imprint	With imprint
Cover	For covering of socket outlets
Protection	Without protective screen

Suitable for

cubyko	
--------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes